## Quick Release Cage Clamp 3/4 dia. Truss Tubes Model #CC0750

-Tapered holes for quick and smooth engage/release of the secondary cage, even in the dark

- -Two locking pins form a rigid connection that maintains your collimation, no creep during the nights viewing
- -Truss poles stay connected in pairs to speed assembly/disassembly
- Compact design for rigidity and damping

Hole pattern for mounting clamps to cage ring
Threaded 1/4-20



www.aurorap.com 6644 SE Jerry Dr. Prineville Oregon 97754\541-362-5965

- \*Material is black anodized aluminum
- \*All stainless steel hardware
- \*Black phenolic knob with brass insert
- \*Black delrin bushings at all joints
- \*Weight of one assembly is 88 grams, 3.2 oz.

Clamping knob is captured, can't be dropped or lost -1/4 dia. Locking pins secure assembly lower ring of cage assembly Tubes pivot to fit truss angle 1 5/8 Tube brackets cap 13/16 from bracket to tubes and nest center of your tubes inside for a rigid non-flexing connection. Tube wall thickness is .049 or .035 Stays mounted Tube connectors are included. Drive connectors into tubes Pair of tubes to grip tube wall release

All dimensions are in inches.

## Alternate method of assembly.

Brackets are turned, allowing tubes to be under the cage ring. This may be helpful depending on your scope design, or to reduce the size of the mirror box.

