## Quick Release Cage Clamp 1-1/2in. dia. Truss Tubes Model #CC1500



www.aurorap.com 6644 SE Jerry Dr. Prineville Oregon 97754 541-362-5965

-Tapered holes for quick and smooth engage/release of the secondary cage, even in the dark

> included. Drive connectors into tubes to grip tube wall

- -Two locking pins form a rigid connection that maintains your collimation, no creep during the nights viewing
- to speed assembly/disassembly

All dimensions are in inches.

1/4 dia. Locking pins

secure assembly -

Tube brackets cap

tubes and nest inside for a rigid non-flexing connection. Tube

wall thickness is


.065 or .049

- Compact design for rigidity and damping

-Truss poles stay connected in pairs

Hole pattern for mounting clamps to cage ring Threaded 1/4-20


- - \*Material is black anodized aluminum
  - \*All stainless steel hardware
  - \*Black phenolic knob with brass insert
  - \*Black delrin bushings at all joints
  - \*Weight of one assembly is 228 grams, 8.0 oz.



All dimensions are in inches.

## Alternate method of assembly.

Brackets are turned, allowing tubes to be under the cage ring. This may be helpful depending on your scope design, or to reduce the size of the mirror box.



CC1500 spec sheet rev4 4-20-20